

GOT2000 Series Protective Sheet for GT27/GT25/GT23/GT2107

User's Manual

_	
GT27-15PSCC	GT25-08PSCC
GT27-15PSGC	GT25-08PSGC
GT25-12PSCC	GT21-07WPSCC
GT25-12PSGC	GT21-07WPSGC
GT25-12WPSCC	GT25-05PSCC
GT25-12WPSGC	GT25-05PSGC
GT25-10PSCC	GT25-05PSCC-2
GT25-10PSGC	GT25-05PSGC-2
GT25-10WPSCC	GT25-12PSCC-UC
GT25-10WPSGC	GT25-10PSCC-UC
	GT25 09DSCC HC

Thank you for purchasing Mitsubishi Electric Graphic Operation

Prior to use, please read both this manual and detailed manual thoroughly to fully understand the product.



	MODEL	G127/G125-PS-U-JE
TZOOO	MODEL CODE	1D7MH9
	IB(NA)-	0800499-G(2101)MEE
© 2013 MITSUBISH	ELECTRIC	CORPORATION

●SAFETY PRECAUTIONS●

(Always read these precautions before using this equipment.)

Before using this product, please read this manual and the relevant manuals introduced in this manual carefully and pay full attention to safety to handle the product correctly.

The precautions given in this manual are concerned with this product In this manual, the safety precautions are ranked as "WARNING" and "CAUTION".

MARNING Indicates that incorrect handling may cause hazardous conditions, resulting in death or severe injury.

Indicates that incorrect handling may cause hazardous A CAUTION Indicates that incone or nationing may also shall injury I or physical damage.

Note that the $extstyle \Delta$ CAUTION level may lead to a serious accident according to the

Always follow the precautions of both levels because they are important to

Please save this manual to make it accessible when required and always forward it

[INSTALLATION PRECAUTIONS]

⚠ CAUTION

When attaching the protective sheet onto the GOT display section, make sure to fit the protective sheet onto the section closely without leaving any air between them. Failure to do so may cause a malfunction/

[STARTUP AND MAINTENANCE PRECAUTIONS]

MARNING

Daily check the protective sheet with eyes. When you find extreme dirt or so the surface, immediately replace it with new one.
Using the productive sheet of decreased visibility may cause a malfunction

IDISPOSAL PRECAUTIONS

⚠ CAUTION

Dispose of this product as industrial waste

[TRANSPORTATION PRECAUTIONS]

⚠ CAUTION

When furnigants that contain halogen materials such as fluorine, chlorine, bromine, and iodine are used for disinfecting and protecting wooden packaging from insects, they cause malfunction when entering our products Please take necessary precautions to ensure that remaining materials from fumigant do not enter our products, or treat packaging with methods other than fumigation (heat method). Additionally, disinfect and protect wood from insects before packing product

<u>Manuals</u>

The following shows manuals relevant to this product.

Manual name	Manual number (Model code)
GOT2000 Series User's Manual (Hardware) (Sold separately)	SH-081194ENG (1D7MJ5)

For detailed manuals and relevant manuals, refer to the e-Manual or PDF manuals stored in the DVD-ROM for the screen design software used.

The latest manuals are also available from MITSUBISHI ELECTRIC FA Globa Website (www.MitsubishiElectric.com/fa).

Referenced Standard: GB/T15969.2

Packing List
After unpacking the box, check that the following products are included.

Model	Product	Quantity
GT27-15PSCC GT27-15PSGC GT25-12PSCC GT25-12PSGC GT25-10PSGC GT25-10PSGC GT25-10PSGC GT25-12WPSGC GT25-12WPSGC GT25-12WPSGC GT25-10WPSCC	GOT2000 series protective sheet	5
GT25-10WPSGC GT25-08PSGC GT25-08PSGC GT21-07WPSGC GT21-07WPSGC GT25-09PSGC GT25-09PSGC GT25-09PSGC2 GT25-05PSGC2 GT25-05PSGC2 GT25-12PSGC-UC GT25-10PSC-UC GT25-10PSC-UC	GOT2000 Series Protective Sheet for GT27/GT25/GT23/GT2107 User's Manual (This manual)	1

1. OVERVIEW

This User's Manual describes GOT 2000 series protective sheet (hereinafter This user's Manual describes GOT 2000 series protective sheet (neighbarianter referred to as the protective sheet). Use the protective sheet to protect the display section surface from scratches and dirt when operating the touch keys on the GOT display section.

2. SPECIFICATIONS

The following shows the performance specifications and models of the protective sheets, and applicable GOT screen sizes. The general specifications for the protective sheet are the same as those of the

For the general specifications of the GOT, refer to the GOT2000 Series User's


The clear protective sheets and the antiglare protective sheets are available. The clear protective sheets have excellent transparency and do not reduce the brightness of the GOT screen. The antiglare protective sheets are anti-reflection coated and suitable for use in an environment where the GOT screen is difficult to see because of the reflected light

Product	Model	Description		
	GT27-15PSGC	For 15"		
	GT25-12PSGC	For 12.1"		
	GT25-10PSGC	For 10.4"	Antiglare type	
	GT25-08PSGC	For 8.4"	Transparent With a hole for the USB	
	GT25-05PSGC	For 5.7" (GT2705)	environmental protection cover	
	GT25-05PSGC-2	For 5.7" (GT2505)		
	GT25-12WPSGC	For 12.1" Wide	Antiglare type	
	GT25-10WPSGC	For 10.1" Wide	Transparent Without a hole for the USB	
	GT21-07WPSGC	For 7" Wide	environmental protection cover*1	
	GT27-15PSCC	For 15"		
Protective sheet	GT25-12PSCC	For 12.1"		
	GT25-10PSCC	For 10.4"	Clear type	
	GT25-08PSCC	For 8.4"	Transparent With a hole for the USB	
	GT25-05PSCC	For 5.7" (GT2705)	environmental protection cover	
	GT25-05PSCC-2	For 5.7" (GT2505)		
	GT25-12WPSCC	For 12.1" Wide	Clear type	
	GT25-10WPSCC	For 10.1" Wide	Transparent Without a hole for the USB	
	GT21-07WPSCC	For 7" Wide	environmental protection cover*1	
	GT25-12PSCC-UC	For 12.1"	Clear type	
	GT25-10PSCC-UC	For 10.4"	Transparent Without a hole for the USB	
	GT25-08PSCC-UC	For 8.4"	environmental protection cover	


*1: The protective sheet is shaped not to cover the USB environmental protection

3. EXTERNAL DIMENSIONS


GT27-15PSCC, GT27-15PSGC, GT25-12PSGC, GT25-12PSGC, GT25-10PSCC, GT25-08PSCC, GT25-08PSGC, GT25-05PSCC, GT25-05PSGC



(2) GT25-12WPSCC, GT25-12WPSGC, GT25-10WPSCC, GT25-10WPSGC, GT21-07WPSCC, GT21-07WPSGC, GT25-12PSCC-UC, GT25-10PSCC-UC, GT25-08PSCC-UC



(3) GT25-05PSCC-2, GT25-05PSGC-2




A	В
392(15.4)	287(11.3)
312(12.3)	234(9.21)
297(11.7)	198(7.80)
299(11.8)	206(8.11)
250(9.84)	173(6.81)
237(9.33)	182(7.17)
187(7.36)	121(4.76)
163(6.42)	127(5.00)
160(6.30)	127(5.00)
	392(15.4) 312(12.3) 297(11.7) 299(11.8) 250(9.84) 237(9.33) 187(7.36) 163(6.42)

Unit: mm (inch)

4. INSTALLATION AND REMOVAL

For attaching and removing the protective sheet, refer to the example of the ${\tt GT2712}.$

1) If the old protective sheet is attached, slowly remove the sheet from the finger grip part of the lower right of the GOT. Clean the GOT surface.



Peel the release paper off the back of the new protective sheet.
 Position the hole for the USB environmental protection cover of the sheet to the USB environmental protection cover of the GOT. If the protective sheet without the hole for the USB environmental p cover is attached, position the sheet from the upper left of the GOT.



3) To attach the protective sheet, attach it from one direction gradually. Make sure to fit the protective sheet onto the joining surface closely without leaving any air

Attach the protective sheet with adding additional pressure sufficiently to the adhesive side of the outer circumference. To hold adequate strength of the adhesive joining, use the GOT after a lapse of



5. PRECAUTIONS FOR USE

1) The protective sheet is consumable supplies If you find scratches or extreme dirt by the periodic check, replace it with new

2) Do not push the protective sheet with something whose the point is sharp, such

as a mechanical pencil or screwdriver.

Doing so may cause scratches or be damaged. 3) Do not wash the protective sheet with using bleach, thinner, organic solvent,

caustic chemical, and others.

Doing so may change in shape or color.

4) Do not expose the protective sheet to direct sunlight. If the protective sheet gets dust, wipe the sheet with a damp cloth.

5) When using GT25-05PSCC-2 or GT25-05PSGC-2, remove the protective film

Country/Region Sales office/Tel

Warranty

Mitsubishi Electric will not be held liable for damage caused by factors found not to be the cause of Mitsubishi Electric; machine damage or lost profits caused by faults in the Mitsubishi Electric products; damage, secondary damage, accident compensation caused by special factors unpredictable by Mitsubishi Electric; damages to products other than Mitsubishi Electric products; and to other duties. ⚠ For safe use This product has been manufactured as a general-purpose part for

general industries, and has not been designed or manufactured to be incorporated in a device or system used in purposes related to

human life.

Before using the product for special purposes such as nuclear power, electric power, aerospace, medicine or passenger movement vehicles, consult with Mitsubishi Electric.

This product has been manufactured under strict quality control. However, when installing the product where major accidents or losses could occur if the product fails, install appropriate backup or failsafe functions in the system.

Country/Region	Sales Office/Tel
USA	Mitsubishi Electric Automation, Inc. 500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A. Tei: +1-847-478-2100
Brazil	Mitsubishi Electric do Brasil Comercio e Servicos Ltda. Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brazil Tei: +55-11-4689-3000
Mexico	Mitsubishi Electric Automation, Inc. Mexico Branch Boulevard Miguel de Cervantes Saavedra 301, Torre Norte Piso 5, Ampliacion Granada, Miguel Hidalgo, Ciudad de Mexico, Mexico, C.P.11520 Tel: +52-55-3067-7512
Germany	Mitsubishi Electric Europe B.V. German Branch Mitsubishi-Electric-Platz 1, 40882 Ratingen, Germany Tei: +49-2102-486-0
UK	Mitsubishi Electric Europe B.V. UK Branch Travellers Lane, UK-Hatfield, Hertfordshire, AL10 8XB, U.K. Tei: +44-1707-28-8780
Italy	Mitsubishi Electric Europe B.V. Italian Branch Centro Direzionale Colleoni - Palazzo Sirio, Viale Colleoni 7, 20864 Agrate Brianza (MB), Italy Tel: +39-039-06531
Spain	Mitsubishi Electric Europe B.V. Spanish Branch Carretera de Rubi, 76-80-Apdo. 420, E-08190 Sant Cugat del Valles (Barcelona), Spain Tel: +34-935-65-3131
France	Mitsubishi Electric Europe B.V. French Branch 25, Boulevard des Bouvets, 92741 Nanterre Cedex, France Tei: +33-1-55-68-55-68
Czech	Mitsubishi Electric Europe B.V. Czech Branch Pekarska 621/7, 155 00 Praha 5, Czech Republic Tel: +420-255 719 200

Tel: +420-255 T19 200
Mitsubish IEectric Turkey A.S. Umraniye Branch
Serifali Mahallesi Nutuk Sokak No.5, TR-34775 Umraniye / Istanbul, Turkey
Tel: +90-216-526-5990
Mitsubishi IEectric Europe B.V. Polish Branch
ul. Krakowska 48, 32-083 Balice, Poland
Tel: +48-12-347-85-00
Mitsubishi Electric (Russia) LLC St. Petersburg Branch
Piskarevsky r. J. bil 2, il "Sch", B.C "Benua", office 720; 195027 St. Petersburg, Russia
Tel: +7-812-633-3497

Adroit Technologies 20 Waterford Office Park, 189 Witkoppen Road, Fourways, South Africa Tel: +27-11-658-8100

Mitsubishi Electric Automation (China) Ltd.
Mitsubishi Electric Automation Center, No.1386 Hongqiao Road, Shanghai, China
Tel: +86-21-3322-3030 SETSUYO ENTERPRISE CO., LTD. 6F, No. 105, Wisgong 3rd Road, Wugu District, New Taipei City 24889, Taiwan Tet: +886-2-2299-2499

Mitsubishi Electric Automation Korea Co., Ltd.
7F to 8F, Gangseo Hangang Xi-tower A, 401, Yangcheon-ro, Gangseo-Gu, Seoul 07:28, Korea
Tel: +82-2-3660-9569

Mitsubishi Electric Asia Pte. Ltd. 307 Alexandra Road, Mitsubishi Electric Building, Singapore 159943 Tel: +65-6473-2308

18. 100-0479-2308 Milsubshi Electric Factory Automation (Thailand) Co., Ltd. 12th Floor, SV.City Building, Office Tower 1, No. 896/19 and 20 Rama 3 Road, Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand Tel: +66-2682-6522 to 31

PT. Mitsubishi Electric Indonesia Gedung Jaya 8th Floor, JL. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia Tel: +62-21 3192-6461

re.: 10-24 1 3194-5491 Missubish Electric Vielnam Company Limited 11th & 12th Floor, Viettel Tower B. 285 Cach Mang Thang & Street, Ward 12, District 10, Ho Chi Minh City, Vietnam. Tel: 494-28-3910-5945 Missubish Electric India Pvt. Ltd. Pune Branch Emerald House, EL-3, J Block, M.I.D.C., Bhosari, Pune - 411026, Maharashtra, India Tel: 491-20-210-0200 าย. ชยา-20-27 เป-2000 MITSUBISHI ELECTRIC AUSTRALIA PTY, LTD. 348 Victoria Road, P.O. Box 11, Rydalmere, N.S.W 2116, Australia Tel: +61-2-9684-7777

MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE : TOKYO BUILDING, 2-7-3 MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN NAGOYA WORKS : 1-14, YADA-MINAMI 5-CHOME, HIGASHI-KU, NAGOYA, JAPAN

When exported from Japan, this manual does not require application to the Ministry of Economy, Trade and Industry for service transaction permission.